

INSTRUCTIONS

Operating the Pneumatic Lock

Benefits of Pneumatic Locks

Enhanced Security.

Keep items secure from theft and unauthorized access.

No Outlet Required.

No electric power is necessary. The pneumatic compressed air system activates the lock.

Unobstructed View.

Hidden lock retains full transparency of the display.

Modern Style.

Clean lines and crisp design.



How to Use the Pneumatic Locks

This display case uses a simple pneumatic locking mechanism that you can easily engage or disengage using the included compressed air can.

1. Locate the Lock and Unlock port connector **under the toe kick or body** of your display case.
2. Insert the compressed air into the appropriate port, lightly pinching the tubing to ensure a good seal.

To lock, apply air into the “lock” port until you hear a click, confirming the lock is secured.

To unlock, apply air to the “unlock” port until you hear a click, confirming the lock has released

